




## SENSOREN




LUMI-TAU-INLINE-SL-IR/IR



LUMI-TAU-INLINE-SL-UV/BL  
LUMI-TAU-INLINE-SL-BL/IR  
LUMI-TAU-INLINE-SL-GN/IR



LUMI-TAU-INLINE-SL-R/IR



SPECTRO-T-1-10-DIF-UV/BL  
SPECTRO-T-1-10-DIF-BL/YL  
SPECTRO-T-1-10-DIF-R/IR  
SPECTRO-T-1-10-DIF-BL/IR

## MOBILE GERÄTE



LUMI-TAU-IR/IR-MOBILE-P  
LUMI-TAU-R/IR-MOBILE-P  
LUMI-TAU-BL/IR-MOBILE-P  
LUMI-TAU-UV/BL-MOBILE-P  
LUMI-TAU-GN/IR-MOBILE-P

SPECTRO-T-1-DIF/0°-UV/BL-MOBILE-P  
SPECTRO-T-1-DIF/0°-BL/YL-MOBILE-P  
SPECTRO-T-1-DIF/0°-R/IR-MOBILE-P  
SPECTRO-T-1-DIF/0°-BL/IR-MOBILE-P

## LABOR - GERÄTE



LUMI-TAU-IR/IR-LAB-LF  
LUMI-TAU-R/IR-LAB-LF  
LUMI-TAU-BL/IR-LAB-LF  
LUMI-TAU-UV/BL-LAB-LF  
LUMI-TAU-GN/IR-LAB-LF

SPECTRO-T-1-DIF/0°-UV/BL-LAB-LF  
SPECTRO-T-1-DIF/0°-BL/YL-LAB-LF  
SPECTRO-T-1-DIF/0°-R/IR-LAB-LF  
SPECTRO-T-1-DIF/0°-BL/IR-LAB-LF



LUMI-TAU-IR/IR-LAB-CMU  
LUMI-TAU-R/IR-LAB-CMU  
LUMI-TAU-BL/IR-LAB-CMU  
LUMI-TAU-UV/BL-LAB-CMU  
LUMI-TAU-GN/IR-LAB-CMU



CALIB-SPECTRO-T-1



CALIB-LUMI-TAU



SPECTRO-T-1-DIF/0°-UV/BL-LAB-CMU  
SPECTRO-T-1-DIF/0°-BL/YL-LAB-CMU  
SPECTRO-T-1-DIF/0°-R/IR-LAB-CMU  
SPECTRO-T-1-DIF/0°-BL/IR-LAB-CMU

## INLINE GERÄTE



SPECTRO-T-1-DIF/0°-UV/BL-INLINE  
SPECTRO-T-1-DIF/0°-BL/YL-INLINE  
SPECTRO-T-1-DIF/0°-R/IR-INLINE  
SPECTRO-T-1-DIF/0°-BL/IR-INLINE



LUMI-TAU-IR/IR-INLINE  
LUMI-TAU-R/IR-INLINE  
LUMI-TAU-BL/IR-INLINE  
LUMI-TAU-UV/BL-INLINE  
LUMI-TAU-GN/IR-INLINE



SI-PPC-500-15"